


DESCRIPTION: QUICK RELEASE - BLACK & METALIZED PLASTIC



9 & 15 POSITION

25 POSITION


37 POSITION

SPECIFICATION:

- MATERIAL
- BLACK PLASTIC: ABS PLASTIC, SICOFLEX, UL 94 V-0
- METALIZED
- PLASTIC: NICKEL OVER COPPER PLATING
- TEMP RATING: -55°C to +125°C

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (4) MOUNTING SCREWS
- (1) STRAIN RELIEF CLAMP
- (2) STRAIN RELIEF SCREWS



955-YYY-YYYRYY1

- SERIES
- POSITIONS
- 009
- 015
- 025
- 037
- MATERIAL
- 010 = PLASTIC
- 020 = METALIZED PLASTIC
- RoHS COMPLIANT
- R = HIGH TEMP. PROCESS
- COLOR
- 01 = BLACK
- 12 = METAL(IZED)
- PUT-UP
- 1 = KIT

DIMENSIONS (IN.)					
No. OF PINS	A	B	C	D	E
09	1.740	0.606	0.984	1.299	0.354
15	1.740	0.606	1.312	1.626	0.394
25	1.740	0.606	1.852	2.165	0.433
37	1.740	0.606	2.500	2.815	0.433

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

CHECKED:

DATE:
04-10-07

DATE:

SCALE:
1 : 1

DWG NO.













SHEET
1

OF
2

REV
3

955-YYY-YYYRYY1

CABLE CLAMPS ORDERED SEPARATELY



P/N 955-09-SR-4-7
CABLE RANGE = 0.157 - 0.276

P/N 955-15-SR-7-10
CABLE RANGE = 0.276 - 0.394

P/N 955-25-SR-9-12
CABLE RANGE = 0.354 - 0.472

P/N 955-37-SR-11-14
CABLE RANGE = 0.433 - 0.551

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 04-10-07	
			CHECKED:		DATE:	
	NorComp		SCALE: 1 : 1	SHEET 2	OF 2	REV 3
DWG NO. 955-YYY-YYYRYY1						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[955-025-010R011](#) [955-015-010R011](#) [955-037-020R121](#) [955-009-020R121](#) [955-009-010R011](#) [955-037-010R011](#)
[955-015-020R121](#) [955-025-020R121](#)