



DESCRIPTION: 971 SERIES D-SUB BACKSHELL

- BACKSHELL KIT INCLUDES:
- (2) BACKSHELL HALVES
 - (2) 4-40 THUMBSCREWS
 - (2) HOUSING SCREWS
 - (1) COMPRESSION RING - VARIOUS SIZES
Ø0.157 [4.0], Ø0.197 [5.0], Ø0.276 [7.0], Ø0.354 [9.0]

NOTE: 9 POSITION HAS ONLY 1 THUMBSCREW
(OPPOSITE CABLE ENTRY)



SERIES	971-YYY-040R011
POSITIONS	009 015 025 037
MATERIAL	040 = ZINC
COLOR:	01 = BLACK
PUT-UPS	1 = KIT

DIMENSIONS (in/mm)				
POS.	A	B	C	D
9	1.220	.984	1.429	.570
	30.99	24.99	36.30	14.48
15	1.556	1.312	1.587	.570
	39.50	33.32	40.30	14.48
25	2.094	1.852	1.587	.570
	53.20	47.04	40.30	14.48
37	2.744	2.500	1.587	.570
	69.70	63.50	40.30	14.48

MATERIAL: DIE CAST ZINC ALLOY
PLATING: BLACK ENAMEL
JACKSCREWS: STEEL - BLACK OXIDE
HOOD SCREWS: STEEL - BLACK OXIDE
COMPRESSION INSERTS: ABS UL 94-HB
OPERATING TEMP: -40°C TO + 120 °C

UNITS = INCHES [MM]

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 6-10-05		
		SCALE NTS		SHEET 1 OF 1		REV 9
		DWG NO. 971-YYY-040R011				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[971-009-040R011](#) [971-015-040R011](#) [971-025-040R011](#) [971-037-040R011](#)