


NOTE:

MATERIAL

HOUSING

FLANGE

CONTACT

SHELL

O-RING

SEALING COMPOUND

HARDWARE

PBT UL94V-0, BLACK

PBT UL94V-0, BLACK

BRASS, PLATING P/N KEY BELOW

STEEL, NICKEL

SILICONE

EPOXY

BRASS; NICKEL PLATED

ELECTRICAL

POWER CONTACT RATED CURRENT

VOLTAGE

INSULATOR RESISTANCE

POWER CONTACT RESISTANCE

WATER PROOF

ENVIRONMENT

OPERATION TEMPERATURE

P/N KEY BELOW

1000 VAC 1 MIN

5 GOhms MIN.

2.0 mOhms MAX.

IP67

-25°C TO +85°C

SERIES _____ CDFS3W3103LYYY

CONTACT TYPE _____

S = SOLDER CUP

POSITION _____

3W3

GENDER _____

1 = MALE

POWER CONTACT AMPERAGE _____

2 = 20 AMPS

4 = 40 AMPS

HARDWARE OPTIONS _____

1 = 4-40 THREADED INSERTS/4-40 JACKSCREWS

CONTACT PLATING OPTIONS _____

1 = GOLD FLASH

2 = 30u" GOLD PLATING

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

04/07/2020

TOLERANCES

X. ±0.40

.X ±0.30

.XX ±0.20

.XXX ±0.10

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

1

DWG NO.

CDFS3W3103LYYY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[CDFS13W3103L411](#) [CDFS3W3103L412](#) [CDFS3W3103L211](#) [CDFS3W3103L212](#) [CDFS13W3103L211](#)
[CDFS13W3103L212](#) [CDFS13W3103L412](#) [CDFS3W3103L411](#)