





HARDWARE OPTIONS



NOTE:

MATERIAL

HOUSING
FLANGE
CONTACT
SHELL
O-RING
SEALING COMPOUND
HARDWARE

PBT UL94V-0, BLACK
PBT UL94V-0, BLACK
BRASS, PLATING P/N KEY BELOW
STEEL, NICKEL
SILICONE
EPOXY
BRASS; NICKEL PLATED

ELECTRICAL

POWER CONTACT RATED CURRENT
VOLTAGE
INSULATOR RESISTANCE
POWER CONTACT RESISTANCE
WATER PROOF

P/N KEY BELOW
1000 VAC 1 MIN
5 GOhms MIN.
2.0 mOhms MAX.
IP67

ENVIRONMENT

OPERATION TEMPERATURE -25°C TO +85°C

SERIES _____ CDFV3W3113LYYY
CDF = COMBO DSUB FLANGE
CONTACT TYPE _____
V = VERTICAL PCB MOUNT
POSITION _____
3W3
GENDER _____
1 = MALE
POWER CONTACT AMPERAGE _____
2 = 20 AMPS
4 = 40 AMPS
HARDWARE OPTIONS _____
1 = 4-40 THREADED INSERTS/4-40 JACKSCREWS
5 = 4-40 THREADED BOARD LOCKS &
4-40 JACKSCREWS
CONTACT PLATING OPTIONS _____
1 = GOLD FLASH
2 = 30u" GOLD PLATING

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
J. KADEL

DATE:
04/07/2020

TOLERANCES

X. ±0.40
.X ±0.30
.XX ±0.20
.XXX ±0.10

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
1 2


REV
1

DWG NO.


CDFV3W3113LYYY

**ø3.20MM HOLES NOT NEEDED FOR "1" HARDWARE OPTION

20 AMP CONFIGURATION



40 AMP CONFIGURATION



RECOMMENDED PCB LAYOUT
*TYPICAL // HOLE SIZE MAY NOT BE SUITABLE FOR YOUR
SPECIFIC APPLICATION

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: J. KADEL
	DATE: 04/07/2020

TOLERANCES	
X.	±0.40
.X	±0.30
.XX	±0.20
.XXX	±0.10

UNITS = mm

NorComp

DO NOT SCALE FROM DRAWING

SCALE: NTS	SHEET 2 OF 2	REV 1
DWG NO. CDFV3W3113LYYY		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[CDFV3W3213L412](#) [CDFV3W3113L212](#) [CDFV3W3113L412](#) [CDFV3W3113L411](#) [CDFV3W3213L211](#)
[CDFV3W3113L251](#) [CDFV3W3213L452](#) [CDFV3W3113L252](#) [CDFV3W3113L452](#) [CDFV3W3113L451](#)
[CDFV3W3213L411](#) [CDFV3W3213L212](#) [CDFV3W3213L251](#) [CDFV3W3213L252](#) [CDFV3W3113L211](#)
[CDFV3W3213L451](#)