




SPECIFICATION:

INSULATOR: PBT GLASS FIBER REINFORCED UL 94VO
CONTACT: BRASS
CONTACT PLATING: GOLD PLATED OVER NICKEL
SHELL: TIN PLATED SHELL
CURRENT RATING: 3 AMP
DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
INSULATION RESISTANCE: 1,000 MegOHMS MIN @500 VDC
TEMPERATURE: -55° C - +105° C


NOTE:

LABEL: YELLOW COLOR WITH BLACK CHARACTORS
ONE SIDE: MINI GENDER CHANGER
OTHER SIDE: U.S.A. PATENT 5199906



| 26-PIN MALE | | 26-PIN MALE |
|-------------|-----|-------------|
| 1 | --- | 1 |
| 2 | --- | 2 |
| 3 | --- | 3 |
| ~ | | |
| 25 | --- | 25 |
| 26 | --- | 26 |
| SHELL | --- | SHELL |

PIN OUT



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN:
C. SMITH

DATE:
10-15-07

CHECKED:

DATE:

SCALE:
1.5 : 1

SHEET
1 OF 1

REV
1

DWG NO.
GCHDLP26M26M

RoHS COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[GCHDLP26M26M](#)