






SPECIFICATION:

INSULATOR: PBT GLASS FIBER REINFORCED
UL 94VO
CONTACT: BRASS
CONTACT PLATING: GOLD PLATED OVER NICKEL
SHELL: TIN PLATED SHELL
CURRENT RATING: 3 AMP
DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
INSULATION RESISTANCE: 1,000 MegOHMS MIN @500 VDC
TEMPERATURE: -55° C - +105° C

NOTE:


LABEL: YELLOW COLOR WITH
BLACK CHARACTORS
ONE SIDE: MINI GENDER CHANGER
OTHER SIDE: U.S.A. PATENT 5199906



15-PIN FEMALE	15-PIN FEMALE
1	1
2	2
3	3
14	
15	
SHELL	SHELL
PIN OUT	

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 05-27-08	
		CHECKED:		DATE:	
		SCALE: 1.5 : 1	SHEET 1 OF 1		REV 0
		DWG NO. GCHDLPF15F15F			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[GCHDLPF15F15F](#)