

SPECIFICATIONS:

MATERIALS:

HOUSING:

PBT, UL94 V-0

CONTACTS:

GOLD FLASH PLATED BRASS

SHELL:

TIN PLATED STEEL

ELECTRICAL:

RATED CURRENT: 3A







250V

WORKING VOLTAGE: 1000 MOhms MIN.

INSULATION RESISTANCE: 15 mOhms MAX.

ENVIRONMENT:

CONTACT RESISTANCE: OPERATING TEMPERATURE: -55°C TO +105°C



UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

10/12/2007

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

1

DWG NO.

GCHDLPF15F15F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[GCHDLPF15F15F](#)