

DIMENSIONS(mm)

SIZE	A	B	C
15	39.50	25.00	16.90
26	48.00	33.30	25.25
44	61.50	47.05	38.95
62	77.80	63.50	55.40

NOTE:

MATERIAL

HOUSING

PBT UL94V-0, BLACK

FLANGE

PBT UL94V-0, BLACK

CONTACT

BRASS, PLATING P/N KEY BELOW

SHELL

STEEL, NICKEL

O-RING

SILICONE

SEALING COMPOUND

EPOXY

HARDWARE

BRASS; NICKEL PLATED

ELECTRICAL

RATED CURRENT

3A

VOLTAGE

1000 VAC 1 MIN

INSULATOR RESISTANCE

5 Gohms MIN.

CONTACT RESISTANCE

10 mOhms MAX.


WATER PROOF

IP67

ENVIRONMENT

OPERATION TEMPERATURE

-25°C TO +85°C



SERIES

HDF = HD DSUB FLANGE

CONTACT TYPE

S = SOLDER CUP

POSITIONS

15

26

44

62

GENDER

1 = MALE

HARDWARE OPTIONS

01 = 4-40 THREADED INSERTS/4-40 JACKSCREWS

CONTACT PLATING OPTIONS

1 = GOLD FLASH

2 = 30u" GOLD PLATING

HDF-SYY-103LYYY

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

03/02/2020

TOLERANCES

X. ± 0.40 .X ± 0.30 .XX ± 0.20 .XXX ± 0.10

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

0

DWG NO.

HDF-SYY-103LYYY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[HDF-S62-103L011](#) [HDF-S62-103L012](#) [HDF-S15-103L012](#) [HDF-S15-103L011](#) [HDF-S26-103L012](#) [HDF-S44-103L011](#)