






DESCRIPTION: RJ-45 TO 25-POSITION MALE D-SUB – PLASTIC & METALIZED PLASTIC

MATERIAL:

HOOD: ABS UL 94V-HB

RJADK25P70808Y1


SERIES _____
POSITIONS _____
25
GENDER _____
P = MALE
D-SUB TERMINALS _____
7 = CRIMP & POKE (CONTACTS PRE-CRIMPED)
MODULAR POSITIONS _____
08
MODULAR POSITIONS LOADED _____
08
COLOR _____
1 = BLACK
2 = METALIZED (SHIELD RATING: 60dB)
3 = GRAY
D-SUB CONTACT PLATING _____
1 = GOLD FLASH
3 = 10μ" DSUB CONTACT // 50μ" RJ-45 CONTACT



RJ45

- 1. BLUE
- 2. ORANGE
- 3. BLACK
- 4. RED
- 5. GREEN
- 6. YELLOW
- 7. BROWN
- 8. WHITE

DB-25M



FRONT VIEW

RoHS COMPLIANT

UNITS = inch

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH
DATE:
05/14/2007

NorComp

SCALE:
NTS
DWG NO.

SHEET
1 OF
1

REV
2

RJADK25P70808Y1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[RJADK25P7080811](#) [RJADK25P7080831](#) [RJADK25P7080821](#)