


DESCRIPTION: M12 // T-SPLITTER // (3X) FEMALE // WIRED THROUGH 1 TO 1



FEMALE

A04	A05	A08	D04	B05

NOTE:

MATERIAL

M12 INSULATOR	PA66, UL94V-0, BLACK
SPLITTER HOUSING	PVC, UL94V-0, BLACK
CONTACT	GOLD FLASH PLATED BRASS
NUT	NICKEL PLATED BRASS

ELECTRICAL

RATED CURRENT	2A(8P) / 4A(4/5P)
VOLTAGE	30V(8P) / 60V(5P) / 250V(4P)
INSULATOR RESISTANCE	100 MOhms MIN.
CONTACT RESISTANCE	10 mOhms MAX.
MATING CYCLES	100 CYCLES MIN

ENVIRONMENT

OPERATION TEMPERATURE	-40°C TO +85°C
IP RATING	IP67 (UNCOUPLED & COUPLED)

RECOMMENDED TORQUE 0.4Nm TO 0.8Nm

SERIES	T58-YYY-FFFR001
CONTACT ARRANGEMENT	T58 = M12 T-SPLIT ADAPTER
A04 = (3X) 4P A-CODE	
A05 = (3X) 5P A-CODE	
A08 = (3X) 8P A-CODE	
D04 = (3X) 4P D-CODE	
B05 = (3X) 5P B-CODE	
GENDER	FFF = FEMALE / FEMALE / FEMALE
CONTACT PLATING	1 = GOLD FLASH

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

12/20/2021

TOLERANCES
.x ±0.5
.xx ±0.2
ANGULAR ±1°

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
2

DWG NO.

T58-YYY-FFFR001

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[T58-A04-FFFR001](#) [T58-A05-FFFR001](#) [T58-A08-FFFR001](#) [T58-B05-FFFR001](#) [T58-D04-FFFR001](#)