

## 2.4GHz : Wi-Fi/BT External Whip Antenna



**PRO-EX-347**

Request Samples



Check Inventory



Ø12 x 28 mm

**RoHS/RoHS II Compliant**

MSL Level = 1

### Features

- Ultra-Compact
- High Reliability/ Sensitivity
- Easy to install
- ROHS Compliant
- Customizable Cable and Connector options

### Applications

- Wi-Fi/Bluetooth/ZigBee/ISM
- IoT/M2M
- Network Devices
- Set top Boxes

### Product Image



## 2.4GHz : Wi-Fi/BT External Whip Antenna



**PRO-EX-347**

Request Samples



Check Inventory



Ø12 x 28 mm

RoHS/RoHS II Compliant

MSL Level = 1


### Electrical Specification

Parameter	Specification			Unit
	Min	Typ	Max	
Operating Frequency	2400		2485	MHz
Return Loss			-6	dB
Polarization	Linear			
Peak Gain			3	dBi
Impedance		50		Ω

### Mechanical & Environmental Specification

Parameter	Specification
Antenna Dimensions	Ø12 x 28 mm
Cable Type	Ø1.13
Cable Length	100 mm
Connector Type	SMA (M)
Mounting Type	Connector
Operating Temperature	-40°C to +85°C

### Product Dimensions



Unit: mm

**ATTENTION:** Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669  
Phone: 512-371-6159 | Fax: 512-351-8858  
For terms and conditions of sales, please visit:  
[www.abracon.com](http://www.abracon.com)

REVISED: 10-25-21

ABRACON IS  
ISO9001-2015  
CERTIFIED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[PRO-EX-347](#)