





PART NO.

75653

SPECIFICATIONS:

WATT: 77
 RESISTANCE: 25 OHMS
 TOLERANCE: 5%
 COATING: CENTOHM
 CORE DIAMETER: 0.750
 CORE LENGTH: 7.25



THIS PRINT AND ALL INFORMATION APPEARING THEREON IS THE PROPERTY OF "OHMITE MANUFACTURING COMPANY". NEITHER THE PRINT NOR THE INFORMATION THEREON MAY BE REPRODUCED OR USED IN ANY MANNER WHATSOEVER OR DIVULGED TO ANY OTHER PERSON UNLESS SPECIFICALLY AUTHORIZED BY "OHMITE MANUFACTURING COMPANY".

OHMITE®

MATERIAL	TOLERANCE ANGLES ± 1/2°
	TWO PLACE DEC. ± .125
	THREE PLACE DEC. ± .062
	FRACTIONS ± 1/64
	FEATURES ON ϕ ± .010
	UNLESS OTHERWISE NOTED
PLATING	DRAWN BY R. GALVAN 122011
HEAT TREAT	CHECKED BY M. WEST 122011
	RELEASED

PART DESCRIPTION
 2-RESISTOR TRACK ASSY

SCALE: FULL **A** DWG. NO. 75653

C	5283	OB	090314
B	4166	OB	112411
A	INITIAL RELEASE	DD	122602
CHG	E. C. N.	BY	DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ohmite:](#)

[75653-25](#)