

AF Series

IEC Inlet Single Phase EMI Filters



The Ohmite AF series range of IEC Inlet type filters come in three designs. They are available with a fuse and switch and are designed to suppress undesirable electrical disturbances in Power Lines. They limit the amplitude of interfering voltages on AC power lines and prevent them from propagating into or out of the filtered equipment.

FEATURES




- Integral IEC Connector
- Excellent performance/size ratio
- Single/Double Fuse Option
- Rated current up to 15 A
- Snap-in or Screw Mount
- High Conducted attenuation performance
- Double Pole/Single Throw Switch
- Medical versions available

APPLICATIONS

- Electrical & Electronic Equipment
- Testing & Measurement Equipment
- Household equipment
- Rack mounting equipment
- Power Systems
- Frequency converters
- Stepper motor drives
- UPS/Inverters



INSERTION LOSS



(continued)

CHARACTERISTICS


Max. Cont. Oper. Voltage	250VAC
Operating Frequency	50/60Hz
Current ratings	AF-A: 1A to 15A @40°C, AF-B: 1A to 6A @40°C; AF-C: 1A to 10A @40°C
High Potential test voltage	L to G 2120VDC for 1 Minute; L to L 1414VDC for 1 Minute
Overload Capability	135% of Rated current for 15 min.
Design	corresponding to UL60939-3, CSA 22.2 No.8-13 and IEC 60939
Flammability	corresponding to UL 94 V-0
Temperature range	-25°C to +85°C
Climatic Category	25/85/21
Enclosure Material	AF-A and B: Aluminium; AF-C: CRCA
Termination	Fastons 6.3 X 0.8mm
Leakage Current	0.34 mA @250VAC

AF Series

IEC Inlet Single Phase EMI Filters

DIMENSIONS


All dimensions in mm; Tolerances according to ISO2768-m



AF Series

IEC Inlet Single Phase EMI Filters

CIRCUIT DIAGRAMS



ORDERING INFORMATION

AF - A 0 2 - S D
 Series Configuration Current Mounting
 A = Inlet filter base
 B = Inlet filter fuse
 C = Inlet filter fuse and switch
 0 = 1A
 2 = 2A
 3 = 3A
 6 = 6A
 10 = 10A
 15 = 15A
 S = Screw mount
 N = Snap-in mount
 Fuse
 D = Dual
 blank = single/none

Part No.	Rated current @40°C	Weight (g)
AF-A01-S	1A	60
AF-A02-S	2A	60
AF-A03-S	3A	60
AF-A06-S	6A	60
AF-A10-S	10A	60
AF-A15-S	15A	60
AF-B01-S	1A	60
AF-B03-S	3A	60
AF-B06-S	6A	60
AF-C01-SD	1A	120
AF-C03-SD	3A	120
AF-C06-SD	6A	120
AF-C10-SD	10A	120

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ohmite:](#)

[AF-A15-S](#) [AF-C10-SD](#) [AF-B06-S](#) [AF-B03-S](#) [AF-A03-S](#) [AF-A10-S](#) [AF-C03-SD](#) [AF-C06-SD](#) [AF-A06-S](#) [AF-B01-S](#)
[AF-C01-SD](#)