


RCS-25

RCS-30


These ratcheting cable slitters are designed to dismantle heavy-duty cables. The RCS-25 and RCS-30 both slit and ring round cables greater than 1" (25 mm) in diameter, and the RCS-30 can also be used to make window cuts in ducts up to 5 mm thick. These slitters feature the following:

- Slits and rings cables made of PVC, PE, rubber, and other jacket materials
- Fixed jaws and ratcheting feature make it easy to grip and slit heavy-duty cable
- Perfect for mid-span or end cable slitting and ringing
- 10, 20, and 30 mm ruler marked on tool for accurate and precise slitting lengths
- Blade is made of steel, ground, and heat-treated for a razor-sharp edge and long term durability
- Replaceable double-ended blade has an adjustable cutting depth of 0 to 5 mm (0" to 0.20"). The RCS-25RB is the replacement blade for the RCS-25 and the RCS-30RB is the replacement blade for the RCS-30.
- The RCS-30 has a unique blade that penetrates duct walls up to 5 mm thick, allowing you to make mid span window cuts in ducts
- RCS-25 - Replacement Blade: RCS-25RB
- RCS-30 - Replacement Blade: RCS-30RB

SPECIFICATIONS	RCS-25	RCS-30	RCS-25RB	RCS-30RB
APPLICATION	Cables	Cables & Ducts	Cables	Cables & Ducts
MINIMUM CABLE DIAMETER	0.98" (25 mm)	0.98" (25 mm)	0.98" (25 mm)	0.98" (25 mm)
BLADE DEPTH	0.00"-0.20" (0 mm-5 mm)	0.00"-0.20" (0 mm-5 mm)	0.00"-0.20" (0 mm-5 mm)	0.00"-0.20" (0 mm-5 mm)
OVERALL LENGTH	6" (152 mm)	6" (152 mm)	1 1/8" (28.6 mm)	1 1/8" (28.6 mm)
WEIGHT	0.4 lb (181.43 g)	0.358 lb (167 g)	0.045 lb (20.41 g)	N/A
UPC #	811490018822	811490018693	811490018839	811490018709

MADE FOR LIFE®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[RCS-25](#)