



Jonard's adjustable wrenches are made of chrome vanadium steel with a chrome plated finish. They are forged and heat treated for maximum strength. Handles are covered with a red vinyl grip for user comfort. The knurled worm gear is precision formed and the operation is smooth and trouble free. For accurate and faster adjustments use the metric or English scales on either side of the jaws. With extra wide jaws, a smaller wrench works on bigger jobs. Great for tight spaces.

Available kit: **AW-6810** Adjustable Wrench Set: 6", 8", & 10" with Extra Wide Jaws.

3-Piece Kit includes:

AW-6 Adjustable Wrench 6" with Extra Wide Jaws

AW-8 Adjustable Wrench 8" with Extra Wide Jaws

AW-10 Adjustable Wrench 10" with Extra Wide Jaws

SPECIFICATIONS	AW-6	AW-8	AW-10	AW-12
JAW CAPACITY	15/16" (24mm)	1-1/8" (29mm)	1-5/16" (33mm)	1-1/2" (38mm)
MATERIAL	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel
FINISH	Chrome	Chrome	Chrome	Chrome
HANDLE GRIP MATERIAL	Vinyl	Vinyl	Vinyl	Vinyl
STANDARDS	ASME B107.8-2003 & ANSI			
OVERALL LENGTH	6" (152mm)	8" (203mm)	10" (254mm)	12" (305mm)
WEIGHT	0.457 lbs (207g)	0.833 lbs (378g)	1.319 lbs (598g)	1.910 lbs (866g)
UPC NO.	811490015395	811490015401	811490015418	811490015388

MADE FOR LIFE®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[AW-8](#) [AW-12](#) [AW-10](#) [AW-6](#)