


CWRR-716

CW-716

CWS-716

Measures 7/16" at both the open end and box end. Both ends have an angle offset (15°) to ease access in confined areas. The box end offers 12 points of contact. Chrome plated, polished to a high gloss finish and made of chrome vanadium steel.

CWRR-716 6 1/2" (165.1mm)

CW-716 6 5/8" long

CWS-716 4" long

SPECIFICATIONS	CWRR-716	CW-716	CWS-716
WRENCH TYPE	Combination, Reversible	Combination	Combination
SIZE	7/16" (11.11mm)	7/16" (11.11mm)	7/16" (11.11mm)
HEAD ANGLE	15 Degrees	15 Degrees	15 Degrees
FINISH	Polished	Polished	Polished
MATERIAL	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel
LENGTH	6 1/2" (165.1mm)	6 5/8" (168.27mm)	4" (101.6mm)
WEIGHT	0.215 lbs (97.52g)	0.174 lbs (78.92 g)	0.111 lbs (50.35 g)
UPC NO.	811490016774	811490011168	811490019881

MADE FOR LIFE®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[CW-716](#) [CWRR-716](#)