



Jonard's cable cutters are made of chrome vanadium steel with induction-hardened cutting edges for maximum strength and durability. These cable cutters feature the following:

- High leverage design for superior cutting ability
- Shear-type jaw for easily cutting through aluminum, copper, and 100-pair 24 AWG cable
- Spring-loaded mechanism to keep the cutters open
- Ergonomically designed handle with dipped plastic grip for greater comfort and torque
- This product is not for use on steel or ACSR type cable

SPECIFICATIONS

CUT TYPE	Cable
CONDUCTOR MATERIAL	Aluminum, Copper
MAXIMUM CABLE DIAMETER	2/0 Copper, 4/0 Aluminum, 100-pair Cable (24 AWG)
JAW LENGTH	1-3/8" (34.93mm)
JAW THICKNESS	1/2" (12.70mm)
JAW WIDTH	13/16" (20.64mm)
MATERIAL	Chrome Vanadium Steel
LENGTH	9-1/4" (234.95mm)
WEIGHT	1.037 lbs
WEIGHT	811490010406

MADE FOR LIFE®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[JIC-63050](#)