



Intelligent, auto-function volt meter is capable of gauging both the required range and the required function based on the test lead input, providing the simplest experience and the most accurate results. Simply plug in the leads and connect to your test subject and let the AMM-600 take the guess work out of testing.

- Tests AC and DC voltage, AC and DC current, resistance, capacitance, frequency, diode, duty cycle, continuity, automatic current input detection, live testing, non-contact voltage detection (NCV)
- Provides maximum/minimum/average readings, relative measurements
- CAT IV 600V, Class 2, Double insulation safety rating
- Backlit display for low light, and highlight environments
- Unique design with grooved housing for superior grip
- Includes hard carrying case

SPECIFICATIONS	
AC CURRENT	600A
AC VOLTAGE	600V
RESISTANCE	4000-40MΩ
CAPACITANCE	4nF-40mF
FREQUENCY	4Hz-4MHz
COUNTS	4000
OVERVOLTAGE CATEGORY	CAT IV 600v
WEIGHT	N/A
UPC #	810053359525



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[AMM-600](#)