



Designed for cutting round holes in ceilings, walls, and floors without making a mess, the AHC-19 is the perfect tool for installing recessed speakers, lighting, or other round objects. This adjustable hole cutter features the following:

- Can be hooked up to vacuums, with 2.5" (63.5 mm) diameter hose nozzles, to suck up debris as you go
- Cuts plywood, sheetrock, plasterboard, and acrylic sheet up to 1 1/16" (27 mm) thick
- Cutting depth is adjustable via hex locknut and compression spring
- Cuts hole sizes from 2.2" to 9" (56 mm - 228.6 mm) in diameter
- Polycarbonate transparent dust shield collects dust and prevents chips from flying into eyes while cutting
- Rubber gasket provides surface protection against damage, tight seal against flat surfaces, and prevents fallout from debris
- Compression spring absorbs vibrations while cutting
- Can be used with any variable-speed drill
- Power drill and vacuum not included with hole cutter

Product Includes:

- 1 Cover, 1 Adjustable Hole Cutter, 1 Vacuum Port, 1 Cap, 1 Nut, 1 Set of Replacement Blades, 1 Hex Key, and a Rugged Carry Case

SPECIFICATIONS	
CUT TYPE	Round Hole
WORKS ON	Plywood, Sheetrock, Plasterboard, Acrylic Sheet
CUTTING DIAMETER RANGE	2.2" - 9" (56 mm-228.6 mm)
VACUUM PORT SIZE	2.5" (63.5 mm)
MAXIMUM CUTTING DEPTH	1.1" (27 mm)
BIT DIAMETER	0.236" (6.0 mm)
BIT LENGTH	2.17" (55 mm)
BIT MATERIAL	Steel
HEX CHUCK SIZE/ARBOR SIZE	3/8" (9.53 mm)
DIMENSIONS	13" x 4.50" x 13" (33 cm x 33 cm x 11.4 cm)
WEIGHT	5.43 lb (2.47 kg)
UPC #	810053350188



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[AHC-19](#)