



These adapters are designed to join two male RG6, RG6 Quad Shield, RG59, RG59 Quad Shield CATV F connectors. These adapters also feature the following:

- For performance up to 3.0 GHz
- Gold-plated contacts for maximum performance
- For use with male RG6, RG6 Quad Shield, RG59, RG59 Quad Shield CATV F connectors

SPECIFICATIONS	
CONNECTOR TYPE	F Female Splice Adapter
STANDARDS	IEC 60169-24
TEMPERATURE RANGE	-40~+85°C
VIBRATION	100 m/s ² (10~500Hz)
IMPEDENCE	75 Ω
FREQUENCY RANGE	DC~1GHz
WORKING VOLTAGE	170V
WITHSTAND VOLTAGE	500V
CENTER CONTACT RES.	≤ 10 mΩ
OUTER CONTACT RES.	≤ 5 mΩ
INSULATION RES.	≥ 1000 MΩ
RETURN LOSS	≥ 25dB
INSERTION LOSS	≤ 0.8 dB
WEIGHT	0.02 lb (9.08 g)
UPC #	810053351703



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[RG-F81](#)