



Perfect for tracing outlets back to the breaker, identifying wiring errors, and testing GFCI outlets ; the GFC-CBF is an all-in-one solution for any troubleshooting task.

- Trace an outlet back to its individual breaker.
- Manually adjustable sensitivity allows finding a breaker quick and easy.
- Easy to read lights make determining faults a breeze
- Durable, hard shell built to withstand a 6.6-foot (2m) drop
- Nominal Voltage: 110/125V AC at 50/60Hz in 3-wire outlet
- Works on GFCI outlets and confirms operation of the ground fault protective device

SPECIFICATIONS	
STANDARDS	ETL
DIMENSIONS	Transmitter:103x56x30mm Reciever: 196x54x28mm
WEIGHT	Transmitter: 80g. Receiver: 133g
UPC #	810132435942



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[CBF-100](#)