


CTW-716312

CTW-71638

Designed for torquing F connectors to a preset torque of 30 in-lb (3.4 N-m), these torque wrenches are perfect for use in high-density locations. Featuring the following:

- Ideal for use in high density locations such as headends.
- Handle has audible click sound that lets you know when the connector is fully torqued to 30 in-lb.
- Turn clockwise to tighten the connector and counterclockwise to remove.
- Preset calibration to 30 in-lb (3.4 N-m) to meet most manufacturers' recommended torque requirements for their F connectors so no adjustments are needed.
- 8" shaft provides easy access to connectors in tight locations
- 12" shaft provides extra length in hard to reach locations.
- Handle has ergonomic rubberized grip for increased comfort and improved leverage.
- CTW-71638 includes: CTW-7168 - 8" Shaft, CTW-H - Handle.
- CTW-716312 includes: CTW-71612 - 12" Shaft, CTW-H - Handle.
- CTW-7163812 includes: CTW-7168 - 8" Shaft, CTW-71612 - 12" Shaft, CTW-H - Handle.

SPECIFICATIONS	CTW-7163812	CTW-71638	CTW-716312	CTW-7168	CTW-71612	CTW-H
PARTS	8" Shaft, 12" Shaft & Handle	8" Shaft & Handle	12" Shaft & Handle	8" Shaft	12" Shaft	Handle
SHAFT LENGTH	8" (20.32 cm) 12" (30.48 cm)	8" (20.32 cm)	12" (30.48 cm)	8" (20.32 cm)	12" (30.48 cm)	N/A
ASSEMBLED LENGTH	8.625" (21.91 cm) 13" (33.0 cm)	8.625" (21.91 cm)	13" (33.0 cm)	N/A	N/A	N/A
SHAFT MATERIAL	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	N/A
WEIGHT	0.428 lb (194 g)	0.304 lb (138 g)	0.326 lb (148 g)	0.090 lb (41 g)	0.117 lb (53 g)	0.212 lb (96 g)
UPC NO.	811490018723	811490018433	811490018426	811490018440	811490018419	811490018402

MADE FOR LIFE®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Jonard Tools:

[CTW-71638](#) [CTW-7168](#) [CTW-71612](#) [CTW-716312](#) [CTW-7163812](#)