



These **PATENTED** slit and ring tools are designed to open fiber jackets and loose buffer tubes to provide easy fiber access. One side of the tool slits fiber jackets and loose buffer tubes, the opposite side rings fiber jackets and loose buffer tubes. All this is done without damage to the fiber. Blades are replaceable. Note: MS-326 is designed for cables used in ducts and microducts.

#### Simple to use:

- Select the correct groove. Grooves marked with the recommended cable size
- Place the cable in the groove to be used
- Note: The arrow on the top of the tool indicates the pulling direction and the line indicates the blade location
- Close the tool making sure lock is engaged and pull to slit the cable
- For ring operation use ring side of tool and repeat steps above, instead of pulling rotate the tool 3-6 times to ring the cable

SPECIFICATIONS	MS-426	MS-326	MS-316	MS-306
DESCRIPTION	Mid Span Slit & Ring Tool (5.8mm-12mm)	Mid Span Slit & Ring Tool (5mm-10mm)	Mid Span Slit & Ring Tool (2.9mm-6.8mm)	Mid Span Slit & Ring Tool (1.2mm-3.3mm)
NO. OF PRECISION GROOVES	8 (4 Slitting, 4 Ringing)	10 (5 Slitting, 5 Ringing)	10 (5 Slitting, 5 Ringing)	12 (6 Slitting, 6 Ringing)
CABLE DIAMETERS (MM <sup>2</sup> )	5.8-6.4, 7.8-8.4, 9.8-10.4, 11.2-12	5.0-5.6, 6.0-6.6, 7.2-7.8, 7.8-8.4, 9.4-10	2.9-3.6, 3.6-4.4, 4.4-5.2, 5.2-6.0, 6.0-6.8	1.2-1.5, 1.5-1.8, 1.8-2.1, 2.1-2.5, 2.5-2.9, 2.9-3.3
CABLE TYPE	Thick-walled jackets (up to 2.0mm thick)	Thin-walled jackets	Outer Jackets, Loose Buffer Tubes	Outer Jackets, Loose Buffer Tubes



#### Replacement Cartridges

JONARD P/N	DESCRIPTION
MS-306RB	Replacement Blades for MS-306
MS-316RB	Replacement Blades for MS-316
MSB-5010	Replacement Blades for MS-326
MS-426RB	Replacement Blades for MS-426

**MADE FOR LIFE®**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[MS-326](#)