



Designed to open the toughest heavy-duty cable and duct jackets, the RCS-50 is perfect for performing lateral and longitudinal cuts on submariner cables, large fiber ducts, or large count telephone cables at least 1 1/2" (3.81 cm) in diameter. This ratcheting cable slitter also features the following:

- Includes a free rugged carrying case, the H-20!
- Fixed jaws and ratcheting feature make it easy to grip and slit heavy-duty cable jackets, including jackets made of HDPE (High Density Polyethylene)
- Works on cables or ducts at least 1 1/2" (3.81 cm) in diameter
- Easy adjustable blade depth adjusts from 1/8" - 3/8" (3.18 mm - 9.53 mm) to handle thick-jacketed cables and ducts
- Stainless steel construction with plated steel and aluminum hardware for maximum durability and corrosion resistance
- Perfect for removing thick cable jackets on large submariner power cables, large telecom cables (600 pair+), large fiber optic ducts, or other large power cables
- Replacement blades available: RCS-30RB

SPECIFICATIONS	
CUT TYPE	Slit, & Ring
MIN. CABLE DIAMETER	1 1/2" (3.81 cm)
BLADE DEPTH	1/8" - 3/8" (3.18 mm - 9.53 mm)
OVERALL LENGTH	9" (22.7 cm)
WEIGHT	1.941 lb (0.868 kg)
UPC NO.	810053350027



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[RCS-50](#) [RCS-50RB](#)