



Perfect for tracing cables up to 7 ft underground, locating breaks, or tracing a circuit back to the breaker; the WCT-700 is an all in one solution for any cable tracing task.

- Trace a cable up to 7 ft underground and 1000 ft long
- Manually adjustable sensitivity allows finding a cable down to 6" radius
- Dual backlit LCD screens with both audible and visual signal strength readouts make finding wires and cables a breeze
- Works on Live or dead wires, with a CAT III 600V rating and a live voltage readout
- 7 Signal modes and 3 signal strengths make locating breaks fast and easy
- Durable construction allows 2m of drop protection

SPECIFICATIONS	
STANDARDS	CAT III 600V
DIMENSIONS	Transmitter: 189x96x48 mm Receiver: 226x68x38 mm
WEIGHT	Transmitter: 532 g with battery. Receiver: 360 g with battery
UPC #	810132436055

MADE FOR LIFE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[WCT-700](#)