


VFL-25

VFL-150

VFL-25125

VFL-25 & VFL-150 - Designed to detect fiber breakpoints, fiber leaks, poor connections, and stress points, this visual fault locator and Visual Fault Locator Kit is perfect for field personnel detecting faults in fiber optic cables.

VFL-25125 - Designed to convert the VFL-25 (or other similar VFLs) from FC to LC, this VFL Adapter is perfect for detecting faults in LC connectorized cables. This adapter features the following:

- 2.5mm ferrule fits snugly into the VFL-25 with a female 1.25mm LC connector on the opposite end

SPECIFICATIONS	VFL-25	VFL-150	VFL-25125
FIBER CONNECTOR	FC, SC, ST	FC, LC, SC, ST	N/A
LIGHT SOURCE	Class IIIA Laser Diode	Class IIIA Laser Diode	N/A
DISTANCE	Up to 5km (3.10 miles)	Up to 5km (3.10 miles)	N/A
WAVELENGTH	650nm	650nm	N/A
WORKING TEMPERATURE	-4 Fahrenheit (-20 Celsius) to 140 Fahrenheit (60 Celsius)	-40 Fahrenheit (-40 Celsius) to 185 Fahrenheit (85 Celsius)	N/A
STORAGE TEMPERATURE	-40 Fahrenheit (-40 Celsius) to 185 Fahrenheit (85 Celsius)	-4 Fahrenheit (-20 Celsius) to 140 Fahrenheit (60 Celsius)	N/A
POWER	2 AAA Batteries	2 AAA Batteries	N/A
BATTERY LIFE	60 hours	60 hours	N/A
WEIGHT	0.15 lbs (68g)	0.16 lbs (72.57g)	0.011 lbs (4.989g)
UPC NO.	811490016026	811490016002	811490016019

MADE FOR LIFE®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[VFL-150](#) [VFL-25125](#) [VFL-25](#)