



The WiSpy® professional and durable inspection camera is ideal for any hard-to-see inspections. The WiSpy® is a contractor-grade inspection camera that gives users the ability to see more; easier, and smarter. With app-controlled variable focus, easy attachment to a variety of extensions, and a free and easy-to-use app for IOS or Android, the WiSpy® gets the job done faster.

- The variable focus function on the app allows clear close-up viewing - as close as 2.5" (6cm) for finer detail. A big help if you need to check for specific detail (part numbers etc.) as part of your job.
- Using the WiSpy® App settings screen, you can choose to have the image view either in normal mode or "always up" mode. In Always up mode, it does not matter which way you have the camera positioned during inspections; it will always display the image in the correct "always up" way.
- The rechargeable battery lasts up to 90 minutes while in use and recharges to 90% in just 60 minutes.
- Crisp clear images with 720p high resolution provides real-time video feed and captures photos directly to an iPhone, Android, or another smart device. View objects closer with the WiSpy® App digital zoom.
- Designed with an integrated right-angle mount eliminating the need for an adapter when peering over obstacles.
- Includes a FREE, easy-to-use app (available on IOS and Android) to connect the WiSpy® to your smart device and control the camera and a Jonard Tools Wristband to keep your hands free!

SPECIFICATIONS	
<b>CAMERA DIMENSIONS</b>	3.25 in x 1.25 in x 1.25 in (8.26 cm x 3.18 cm x 3.18 cm)
<b>CAMERA WEIGHT</b>	0.1 lbs (45.4 g)
<b>WIRELESS RANGE</b>	Up to 50' (15 m) line of sight
<b>OPERATING TIME</b>	Up to 90 minutes (LED's on medium brightness setting)
<b>CHARGE UP TIME</b>	Around 80 minutes (95% charged in 60 minutes)
<b>FREQUENCY</b>	2.4 GHz
<b>OPERATING VOLTAGE</b>	5V DC
<b>OPERATING TEMPERATURE</b>	32°F to 95°F (0°C to 35°C)
<b>STORAGE TEMPERATURE</b>	-4°F to 113°F (-20°C to 45°C )
<b>WATER RESISTANCE</b>	IP67 Rated
<b>CAMERA RESOLUTION</b>	720p HD
<b>DIMENSIONS</b>	11 in x 5 in x 2 in (27.94 cm x 12.7 cm x 5.08 cm)
<b>WEIGHT</b>	1.4 lbs (635 g)
<b>UPC #</b>	810053350133

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[CF-200](#)