

WSU-30M - Wrap-Strip-Unwrap Tool, 30 AWG - Data Sheet

Each WSU wire wrapping tool wraps, unwraps and even strips the appropriate wire diameter with a unique built-in stripper blade. Ideal for bench use or tool kit in all service and repair applications. In addition to versatility, convenience, and reliability, the WSU Series offers exceptional value. This tool is recommended for .025" square terminals on .100" centers, Modified Wrap, Gauge 30 AWG, Terminal Hole Diameter 0.036 inches, Terminal Hole Depth 1.5 inches, Outside Diameter 0.125 inches, Square Post 0.025 inches. Unwrap side: Terminal Hole Depth, 1 inch, Outside Diameter 0.125 inches.



Specifications	
Wrap Type	Modified
Wire Gauge	30 AWG (0.25 mm)
Maximum Insulation Diameter	0.021" (0.53 mm)
Terminal Hole Dia.	0.036" (0.91 mm)
Terminal Hole Depth	1.50" (38.1 mm)
Outside Diameter	.125" (3.2mm)
Wrap Post Size	0.025" (0.63 mm)
Functions	Wrap, Unwrap, and Strip
For Use With	.025" (0.63 mm) square terminals on .100" (2.54 mm) center to center of the pins.
Weight	0.076 lbs
UPC No	811490011335

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[WSU-30M](#)