

KB24 - Wire Wrapping Bit, 24 AWG - Data Sheet

Fully compatible with any make or model wire wrapping tool. Gauge Size: 24 AWG. Wrap Type: Regular. Minimum Terminal Diagonal Inches: 0.055. Max Terminal Diagonal Inches: 0.074. Terminal Hole Depth Inches: 0.075. Effective Radius Inches: 0.1. Terminal Hole Diameter Inches: 0.075. Compatible Sleeve Part #: P2426.



Specifications	
Wrap Function	Wrap
Wrap Type	Regular
Wire Gauge	24 AWG (0.5 mm)
Maximum Terminal Diagonal	0.074" (1.87 mm)
Minimum Terminal Diagonal	0.055" (1.39 mm)
Terminal Hole Depth	0.074" (1.87 mm)
Terminal Hole Dia.	0.075" (1.9 mm)
Effective Radius	0.100" (2.54 mm)
Wrap Post Size	0.045" (1.14 mm)
Sleeve Part No.	P2426 and P2426INS (Sold Separately)
Length	3" (76.2mm)
Weight	0.056 lbs
UPC No.	811490013230

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[KB24](#)