

KB26 - Wire Wrapping Bit, 26 AWG - Data Sheet

3 inch Wire Wrapping Bit. Fully compatible with any make or model wire wrapping tool. Gauge Size: 26 AWG. Wrap Type: Regular. Minimum Terminal Diagonal Inches: 0.058. Max Terminal Diagonal Inches: 0.073. Terminal Hole Depth Inches: 1. Effective Radius Inches: 0.1. Terminal Hole Diameter Inches: 0.075. Compatible Sleeve Part# P2426



Specifications	
Wrap Function	Wrap
Wrap Type	Regular
Wire Gauge	26 AWG (0.40 mm)
Minimum Terminal Diagonal	0.058" (1.47 mm)
Maximum Terminal Diagonal	0.073" (1.85 mm)
Terminal Hole Depth	1" (25.4 mm)
Terminal Hole Dia.	0.075" (1.9 mm)
Effective Radius	0.100" (2.54 mm)
Wrap Post Size	0.045" (1.14 mm)
Sleeve Part No.	P2426 and P2426INS (Sold Separately)
Length	3" (76.2mm)
Weight	0.056 lbs
UPC No.	811490013360

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[KB26](#)