

KT24Y - KB24/SW-2426 Set - Data Sheet

Enjoy the convenience of pre-assembled wire wrapping bit and sleeve sets with insulated color-coded sleeves for easy identification of wire sizes based on color. Set includes KB24 Bit and SW-2426 Sleeve (Yellow). For 24 AWG wire.



Specifications	
Wrap Function	Wrap
Wrap Type	Regular
Wire Gauge	24 AWG (0.5 mm)
Minimum Terminal Diagonal	0.055" (1.39 mm)
Maximum Terminal Diagonal	0.074" (1.87 mm)
Terminal Hole Depth	0.75" (19.05 mm)
Terminal Hole Dia.	0.075" (1.9 mm)
Effective Radius	0.100" (2.54 mm)
Wrap Post Size	0.045" (1.14 mm)
Length	3" (76.2mm)
Weight	0.046 lbs
UPC No.	811490015678

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[SW-2426](#) [KT24Y](#)