

WB2426M - Wire Wrapping Bit, 24-26 AWG - Data Sheet

3 inch Wire Wrapping Bit. Fully compatible with any make or model wire wrapping tool. Gauge Size: 24-26 AWG. Wrap Type: Modified. Max Insulation Diameter “: 0.046. Minimum Terminal Diagonal “: 0.054. Max Terminal Diagonal “: 0.073. Terminal Hole Depth “: 0.75. Effective Radius “: 0.118. Terminal Hole Diameter “: 0.075. Compatible Sleeve Part #: P2224.



Specifications	
Wrap Function	Wrap
Wrap Type	Modified
Wire Gauge	24-26 AWG (0.50-0.40 mm)
Maximum Insulation Diameter	0.046" (1.17mm)
Minimum Terminal Diagonal	0.054" (1.37 mm)
Maximum Terminal Diagonal	0.073" (1.85 mm)
Terminal Hole Depth	0.75" (19.05 mm)
Terminal Hole Dia.	0.075" (1.9 mm)
Effective Radius	0.118" (2.99 mm)
Wrap Post Size	0.045" (1.14 mm)
Features	Provides 1.5 to 2 turns of insulation
Sleeve Part No.	P2224 and P2224INS (Sold Separately)
Length	3" (76.2mm)
Weight	0.057 lbs
UPC No	811490013216

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[WB2426M](#)