

## WB3032MIL - Wire Wrapping Bit, 30-32 AWG - Data Sheet

Fully compatible with any make or model wire wrapping tool. Gauge Size: 30-32 AWG. Wrap Type: Modified. Max Insulation Diameter “: 0.027. Minimum Terminal Diagonal “: 0.034. Max Terminal Diagonal “: 0.038. Terminal Hole Depth “: 0.75. Effective Radius “: 0.064. Terminal Hole Diameter “: 0.04. Provides 2.5 turns of insulation. Compatible Sleeve Part #: P3032.



| Specifications              |                                      |
|-----------------------------|--------------------------------------|
| Wrap Function               | Wrap                                 |
| Wrap Type                   | Modified                             |
| Wire Gauge                  | 30-32 AWG (0.25-0.20 mm)             |
| Maximum Insulation Diameter | 0.027” (0.69 mm)                     |
| Minimum Terminal Diagonal   | 0.034” (0.86 mm)                     |
| Maximum Terminal Diagonal   | 0.038” (0.96 mm)                     |
| Terminal Hole Depth         | 0.75” (19.05 mm)                     |
| Terminal Hole Dia.          | 0.040” (1.02 mm)                     |
| Effective Radius            | 0.064” (1.62 mm)                     |
| Wrap Post Size              | 0.025” (0.63 mm)                     |
| Features                    | Provides 2.5 turns of insulation     |
| Sleeve Part No.             | P3032 and P3032INS (Sold Separately) |
| Length                      | 3” (76.2mm)                          |
| Weight                      | 0.049 lbs                            |
| UPC No                      | 811490013452                         |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[WB3032MIL](#)