

MicroFine Cartridges











For MicroFine Solder Handpiece & Tweezers



Temperature Guide

	Max. Temp.	Application
MFT-6 / MFTC-6	675 °F / 357 °C	Temperature sensitive applications
MFT-7 / MFTC-7	775 °F / 413 °C	Most general applications
MFT-8/MFTC-8	875 °F / 468 °C	Ceramic and High Thermal Demand

MicroFine Solder Tip Cartridges for MX-H9-MFH & CV-H9-MFH Handpiece

	Part Number	Geometry	Dimensions
	MFTC-6CH5002 MFTC-7CH5002 MFTC-8CH5002	Chisel	0.2 mm x 5 mm
	MFTC-6CH5004 MFTC-7CH5004 MFTC-8CH5004	Chisel	0.4 mm x 5 mm
	MFTC-6CH5006 MFTC-7CH5006 MFTC-8CH5006	Chisel	0.6 mm x 5 mm
	MFTC-6CH5008 MFTC-7CH5008 MFTC-8CH5008	Chisel	0.8 mm x 5 mm
	MFTC-6CH5012 MFTC-7CH5012 MFTC-8CH5012	Chisel	1.2 mm x 5 mm
	MFTC-6CN5001 MFTC-7CN5001 MFTC-8CN5001	Conical	0.1 mm x 5 mm
	MFTC-6CNR5001 MFTC-7CNR5001 MFTC-8CNR5001	Conical Reach	0.1 mm x 5 mm
	MFTC-6CN5003 MFTC-7CN5003 MFTC-8CN5003	Conical	0.3 mm x 5 mm
	MFTC-6CN5005 MFTC-7CN5005 MFTC-8CN5005	Conical	0.5 mm x 5 mm
	MFTC-6CNB4501 MFTC-7CNB4501 MFTC-8CNB4501	Conical Bent	0.1 mm x 4.5 mm

MicroFine Cartridges

For MicroFine Solder Handpiece & Tweezers



	MFTC-6CNBR4501 MFTC-7CNBR4501 MFTC-8CNBR4501	Conical Bent Reach	0.1 mm x 4.5 mm
	MFTC-6CNB5602 MFTC-7CNB5602 MFTC-8CNB5602	Conical Bent	0.2 mm x 5.6 mm
	MFTC-6CNB4503 MFTC-7CNB4503 MFTC-8CNB4503	Conical Bent	0.3 mm x 4.5 mm
	MFTC-6CNB4505 MFTC-7CNB4505 MFTC-8CNB4505	Conical Bent	0.5 mm x 4.5 mm
	MFTC-6HF5006 MFTC-7HF5006 MFTC-8HF5006	Hoof	0.6 mm x 5 mm
	MFTC-6CC5007 MFTC-7CC5007 MFTC-8CC5007	Chisel Slot	0.7 mm x 5 mm x 1 mm

MicroFine Solder Tip Cartridges for MX-H10-MFT & CV-H10-MFT Tweezers

	Part Number	Geometry	Dimensions
	MFT-6CH9006 MFT-7CH9006 MFT-8CH9006	Chisel	0.6 mm x 9 mm
	MFT-6CH9008 MFT-7CH9008 MFT-8CH9008	Chisel	0.8 mm x 9 mm
	MFT-6PW5403 MFT-7PW5403 MFT-8PW5403	Power Wedge Blade	0.3 mm x 5.4 mm
	MFT-6CNB6204 MFT-7CNB6204 MFT-8CNB6204	Conical Bent	0.4 mm x 6.2 mm
	MFT-6CNB6802 MFT-7CNB6802 MFT-8CNB6802	Conical Bent	0.2 mm x 6.8 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Metcal:](#)

[MFTC-7CH5002](#) [MFTC-7CC5007](#) [MFTC-7CH5008](#) [MFT-6PW5403](#) [MFTC-7CNB4503](#) [MFTC-7CN5005](#) [MFTC-6CN5003](#) [MFT-7CNB6204](#) [MFTC-6CNR5001](#) [MFTC-7CN5001](#) [MFTC-6CNBR4501](#) [MFT-7PW5403](#) [MFTC-6CH5002](#) [MFTC-7CNB5602](#) [MFTC-6CNB5602](#) [MFTC-6CNB4503](#) [MFT-6CH9008](#) [MFTC-7CH5012](#) [MFT-7CH9006](#) [MFTC-6CN5001](#) [MFTC-6CN5005](#) [MFTC-6CH5006](#) [MFT-6CNB6204](#) [MFTC-7CH5004](#) [MFTC-6CC5007](#) [MFTC-6CNB4505](#) [MFTC-7CNBR4501](#) [MFT-6CNB6802](#) [MFTC-7CNB4501](#) [MFTC-6CH5008](#) [MFTC-7CH5006](#) [MFTC-6CNB4501](#) [MFTC-7CNB4505](#) [MFTC-6CH5004](#) [MFTC-6HF5006](#) [MFT-7CH9008](#) [MFT-6CH9006](#) [MFTC-6CH5012](#) [MFT-7CNB6802](#) [MFTC-7CNR5001](#) [MFTC-7HF5006](#) [MFTC-7CN5003](#)