

Gladius G1056

10.4" AMD T56N Rugged Tablet PC



Features

- 10.4" AFFS+ TFT Active Matrix with Resistive and Digitizer Touch Screen
- AMD G-Series G-T56N Accelerated Processing Unit
- Integrated 4GB DDR3-1333 Memory and 32GB 1.8" SATA SSD Drive
- Multi Connectivity (HSUPA 3.75G, WLAN, Gigabit Ethernet, Bluetooth)
- Intergrated Dual 5.0 Megapixel Auto Focus CMOS Cameras and RFID
- Hot-swappable redundant dual batteries
- AMD Radeon™ 6320 with DirectX® 11, OpenGL™ 4.1 and OpenCL™ 1.1 Support

System

CPU	AMD G-Series G-T56N 1.65GHz processor
Graphics Controller	AMD Radeon™ HD 6320
Memory	4GB DDR3 SO-DIMM memory module installed
Chipset	AMD Platform Control Hub A50M
BIOS	AMI Aptio® UEFI BIOS
Audio	1 x Integrated microphone
	2 x Integrated 2W speakers
	1 x Earphone jack
Storage	1 x 32GB 1.8" SATA SSD installed

Peripherals and Devices

Camera	1 x 5.0 megapixel front AF CMOS camera (optional) 1 x 5.0 megapixel rear AF CMOS camera
RFID	Integrated 13.56MHz, ISO 15693/14443A/14443B RFID Reads (optional)
Wi-Fi	Integrated WLAN 802.11 a/b/g/n
Bluetooth	Integrated Bluetooth 2.1 + EDR
GSM/UMTS	Optional HSUPA module (3.75G) for GSM/GPRS/EDGE, EV-DO networks

I/O Interface

USB Port	4 x USB 2.0 ports
Serial Port	1 x RS-232 port (optional)
Ethernet	1 X RJ45 GbE LAN
Docking Port	1 x 35-pin pogo connector for docking connection
Video Port	1 x VGA; 1 x mini DisplayPort

Button & Indicator

Function Key	1 x 5-way function key
Power Button	1 x Power on/off button
LED	4 x LEDs (Power, Battery Status, Wi-Fi/RFID, Bluetooth)

Touch Screen

Type	Analog Resistive
Controller Interface	USB Interface
Digitizer	Electromagnetic digitizer with batter-free pen

LCD Display

Size/Type	10.4" AFFS+ TFT Active Matrix Panel
Max. Resolution	1024 (H) x 768 (V)
Luminance	340 cd/m²
Contrast Ratio	600:1
View Angle (U/D/R/L)	89°/89°/89°/89°
Backlight Type	LED

Power Supply

Adapter Input	100 ~ 240VAC (Full Range)
Adapter Output	19VDC, 4.74A, 90W
Battery Type	Li-battery pack
Battery Capacity	2 x 2500mAh 4-cell external battery packs
Battery Operating Time	6 hours (typ.)

Mechanical & Environmental

Operating Temp.	-20 ~ 45°C (-4 ~ 113°F)
Storage Temp.	-20 ~ 60°C (-4 ~ 140°F)
Discharging Temp.	-20 ~ 40°C (-4 ~ 104°F)
Charging Temp.	0 ~ 40°C (32 ~ 104°F)
Operating Humidity	10 ~ 95% @ 45°C (non-condensing)
Dimensions (W x D x H)	266.8 x 257.7 x 67.7 mm (10.5" x 10.1" x 2.7")
Gross Weight	1.8 kg (3.9 lb)
Vibration	3 Grms/ 5 ~ 500Hz/ random operation
Shock	40G peak acceleration (11 ms duration)
Transit Drop	3ft. (90cm), except the front side
IP Rating	IP54 (Front panel only)
Regulatory	CE/FCC Class B, VCCI certified


OS Support

Windows 8 Embedded / Windows 8 Professional
Windows 7 Embedded / Windows 7 Professional
Windows XP Embedded / Windows XP Professional

Ordering Information

G1056	10.4" AMD G-Series T56N rugged tablet PC with WiFi, Bluetooth, Digitizer and Rear Camera
--------------	--

Dimensions



Standard Accessories

PAC-G090W	20V/4.5A 90W AC/DC Adapter Kit	
Digitizer Pen	Digitizer Pen Kit	
BAT-G1056	2 x Black 2500mAh External Battery Kits	

Optional Accessories

PAC-G090W	20V/4.5A 90W AC/DC Adapter Kit	
eBATB-1056	External Battery (Black) Kit for G1056	
PEN-1056	Battery-free Digitizer Pen Kit	
SST-1056	Shoulder Strap, 128 x 3.7cm	
WMC-1056	Wall-Mount Cradle for G1056	
CHR-1056	Dual-Bay Battery Charger for G1056	

Optional Configuration (CTOS* Kit)

CAM50F-1056	5.0M Front CMOS Camera Kit	
RFID-1056	13.56MHz RFID Kit	
HSUPA-1056	3.75G HSUPA Wireless Kit	

*CTOS means *Configure-to-Order Service*.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ARBOR Technology:](#)

[G1056](#)