


EasyBoard-650E

Wide-Range Temperature Intel® Atom™ Processor N2600/D2550
3.5" Compact Board



Features

- Soldered onboard Intel® Atom™ Processor N2600/D2550
- Single Channel 18/24-bit LVDS and DVI-I Port supported
- RS-485 Auto-flow Control supported
- **Wide-Range Operating Temp.: -40 ~ 85°C**

System

Processor	Soldered onboard Intel® Atom™ Processor N2600 1.6GHz/ D2550 1.86GHz
Chipset	Intel® PCH NM10
Memory	1 x DDR3 SO-DIMM socket, supporting up to 2GB 1067MHz SDRAM
BIOS	AMI BIOS
Watchdog Timer	1~255 levels reset

I/O

Super IO Chipset	Fintek F81866
Serial Port	1 x RS-232 1 x RS-232/422/485 selectable
Keyboard & Mouse	USB interface Keyboard/ Mouse
USB 2.0	6 x USB 2.0 ports
Expansion	1 x Mini-card socket
Storage	1 x Serial ATA ports with 300MB/s HDD transfer rate 1 x CFast socket
Ethernet Chipset	2 x Intel® 82583V PCIe GbE controllers
Digital I/O	8-bit Programmable
Audio Interface	Realtek® ALC662 5.1 Channel HD Audio CODEC, Mic-in/ Line-in/ Line-out

Display

Graphic Chipset	Integrated Intel® GMA 3650 (D2550)/ GMA 3600 (N2600)
Graphic Interface	DVI-I: Analog RGB with resolution up to 1920x1200 or DVI up to 1920x1200 LVDS: Single Channel 24-bit LVDS (D2550) Single Channel 18-bit LVDS (N2600)


OS Support

Windows 7

Mechanical & Environmental


Power Input	DC 12V
Power Consumption	1.26A@+12V with N2600 (Typical) 1.42A@+12V with D2550 (Typical)
Operating Temp.	-40 ~ 85°C (-40 ~ 185°F)
Operating Humidity	10 ~ 95% @ 85°C (non-condensing)
Dimension (L x W)	146 x 102 mm (5.7" x 4.0")

Dimensions





Block Diagram



Ordering Information

EasyBoard-650E (BTO) Intel® Atom™ Processor N2600/ NM10 WT 3.5" compact board

Optional Accessories

CBK-06-2501-00	Cable Kit
	1 x Serial port cable
	1 x Audio cable
	2 x USB cables
	1 x SATA cable
	1 x SATA power cable

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ARBOR Technology:](#)

[EasyBoard-650E](#)