


EmETX-a58M1

ETX

AMD G-series Processor G-Series ETX CPU Module



Features

- Soldered onboard AMD G-series Processor GX-212JC/218GL
- Dual Channels 24-bit LVDS, Analog RGB and DDI Port
- **Extended Operating Temp.: 0 ~ 60°C**

System

CPU	Soldered onboard AMD G-Series Processor GX-212JC/GX-218GL
System Memory	1 x DDR3 SO-DIMM socket, supporting up to 8GB 1333MT/s SDRAM
BIOS	AMI BIOS
Watchdog Timer	1~255 levels reset

I/O

Super IO Chipset	Fintek F71869ED
Serial Port	1 x RS-232 1 x RS-232/422/485 (by Carrier Board)
Parallel Port	SPP/EPP/ECP mode selectable
KB/MS	PS/2 interface for keyboard and mouse
USB 2.0	4 x USB 2.0 ports
Expansion	4 x PCI (OEM request)
Storage	2 x Serial ATA ports with 600MB/s HDD transfer rate Two PATA ports via JMB368 PCIe1 to PATA controllers
Ethernet Chipset	1 x Realtek RTL8105E PCIe 10/100Base-T Ethernet controller
Audio	Realtek ALC662 HD Audio CODEC, Mic-in/ Line-in/ Line-out

Display

Graphic Chipset	Integrated in AMD Radeon™ HD 8000E Graphics
	Analog RGB/DVI: Analog RGB
Graphic Interface	LCD: Dual Channels 24-bit LVDS DDI port: 1 x DDI port


OS Support

Windows 7
Windows 10
Linux

Mechanical & Environmental

Power Requirement	DC 5V, 5VSB
Power Consumption	2.66A@5V(GX-212JC typical)
Operating Temp.	0 ~ 60°C (0 ~ 140°F)
Operating Humidity	0 ~ 95% @ 60°C (non-condensing)
Dimensions (L x W)	114 x 95 mm (4.5" x 3.7")


Dimensions



Unit:mm



Block Diagram



Ordering Information

EmETX-a58M1-212JC	AMD GX-212JC ETX 3.02 CPU module
EmETX-a58M1-218GL	AMD GX-218GL ETX 3.02 CPU module

Optional Accessories

HS-58M1-F2	Heat Spreader; Threaded standoffs, 114*95*9mm, W/PAD
HS-58M1-C1	Heat Spreader; 114*95*28mm, W/FAN
PBE-1000 R2.1	ETX evaluation carrier board in ATX form factor
CBK-05-100-00	Cable kit 1 x FDD cable 3 x COM port cables 1 x USB cable 2 x IDE cables 1 x TV-out cable

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ARBOR Technology:](#)

[EmETX-a58M1-212JC](#) [HS-58M1-F2](#) [HS-58M1-C1](#) [EmETX-a58M1-218GL](#)