



ODB1232 Series



DC Blower - 12, 24V
120x32mm (4.7"x 1.25")



Frame & Impeller	PBT, UL94V-O plastic	Available Options: Tachometer (FG) Alarm (RD) 48V available <u>Life Expectancy (L10)</u> Ball Bearing 50,000 hours <u>Operating Temperature</u> Ball Bearing -10C ~ +70C	
Connection	2x Lead wires 24AWG		
Motor	Brushless DC, auto restart, IC protected		
Bearing System	Dual Ball		
Insulation Resistance	10M ohm between leadwire and frame (500VDC)		
Dielectric Strength	1 second at 500 VAC, max leakage - 500 MicroAmp		
Storage Temperature	-30C ~ +90C		

Model Number	Speed (RPM)	Airflow (CFM)	Noise (dB)	Volts DC	Voltage Range	Amps	Max. Static Pressure ("H2O)
ODB1232-12HB	2600	32	55	12	7~14	0.81	0.90
ODB1232-12MB	2300	29	49	12	7~14	0.50	0.84
ODB1232-12LB	2100	26	48	12	7~14	0.41	0.67
ODB1232-24HHB	3100	38	57	24	18~28	0.68	1.41
ODB1232-24HB	2600	32	55	24	18~28	0.43	0.90
ODB1232-24MB	2300	29	49	24	18~28	0.36	0.84
ODB1232-24LB	2100	26	48	24	18~28	0.25	0.67

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[ODB1232-24MB](#) [ODB1232-24HB](#) [ODB1232-24HHB](#) [ODB1232-12LB](#) [ODB1232-12MB](#) [ODB1232-12HB](#) [ODB1232-24LB](#) [ODB1232-48HB](#) [ODB1232-48LB](#) [ODB1232-48MB](#)