

# FAN CORDS



SPT-1, 2x18 AWG, 105°C UL/cUL Cordage

HEAD STYLE	# OF HEADS	LEAD LENGTH	TERMINATION
<b>C45</b>	<b>3DC</b>	<b>72</b>	<b>P</b>
C45 = 45 deg head	Blank = 1	Lead length in inches. 12" increment is standard for stock product	Blank = Blunt Cut
C90 = 90 deg head	2DC = 2		ST = Stripped and Tinned
C180 = straight	3DC = 3		P = NEMA 1-15P AC plug added
C180T = "T" shape	4DC = 4		EURO = European Type F Plug
	6DC = 6		
	9DC = 9		

Multi-head cords allow for multiple connections of fans to a single power source. Product is available from stock in 2, 3, 4, 6 and 9 head configurations with lead lengths ranging from 12"-12'. Each head is separated by 12" of cord. Standard product is blunt cut, but cords are available with AC plugs on request for an additional charge.



Model Number	Head Style	Number of Heads	Lead Length (in)	Termination
<b>12 INCH LEAD</b>				
C45-12	45°	1	12	Blunt Cut
C90-12	90°	1	12	Blunt Cut
C180-12	Straight	1	12	Blunt Cut
C180T-12	"T"	1	12	Blunt Cut
<b>24 INCH LEAD</b>				
C45-24	45°	1	24	Blunt Cut
C45-24P	45°	1	24	AC Plug
C45-2DC-24	45°	2	24	Blunt Cut
C45-3DC-24	45°	3	24	Blunt Cut
C45-4DC-24	45°	4	24	Blunt Cut
C45-6DC-24	45°	6	24	Blunt Cut
C45-9DC-24	45°	9	24	Blunt Cut
C90-24	90°	1	24	Blunt Cut
C180-24	Straight	1	24	Blunt Cut
C180T-24	"T"	1	24	Blunt Cut
<b>36 INCH LEAD</b>				
C45-36	45°	1	36	Blunt Cut
C90-36	90°	1	36	Blunt Cut
C180-36	Straight	1	36	Blunt Cut
C180T-36	"T"	1	36	Blunt Cut
<b>48 INCH LEAD</b>				
C45-48	45°	1	48	Blunt Cut
C45-48P	45°	1	48	AC Plug
C90-48	90°	1	48	Blunt Cut
C180-48	Straight	1	48	Blunt Cut
C180T-48	"T"	1	48	Blunt Cut
<b>72 INCH LEAD</b>				
C45-72	45°	1	72	Blunt Cut
C45-72P	45°	1	72	AC Plug
C45-3DC-72P	45°	3	72	AC Plug
C90-72	90°	1	72	Blunt Cut
C90-72P	90°	1	72	AC Plug
C180-72	Straight	1	72	Blunt Cut
C180T-72	"T"	1	72	Blunt Cut
<b>144 INCH LEAD</b>				
C45-144	45°	1	144	Blunt Cut
C45-144P	45°	1	144	AC Plug
C45-2DC-144P	45°	2	144	AC Plug
C90-144P	90°	1	144	AC Plug

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Orion Fans:

[C45-2DC-84](#) [C45-36](#) [C45-48](#) [C45-12](#) [C45-24](#) [C180T-72](#) [C180T-12](#) [C180-48](#) [C180-24](#) [C180-12](#) [C180-72](#) [C180-36](#) [C90-36](#) [C90-72](#) [C90-48](#) [C90-12](#) [C90-24](#) [C180T-24](#) [C180T-36](#) [C180T-48](#) [C45-3DC-144P](#) [C45-72](#) [C45-48P](#) [C90-144P](#) [C45-24P](#) [C45-72P](#) [C45-2DC-24P](#) [C45-144P](#) [C45-4DC-72P](#) [C45-60P](#) [C45-2DC-72P](#) [C45-144](#) [C90-80](#) [C45-2DC-144P](#) [C45-2DC24-72P](#) [C90-80P](#) [C45-2DC-60](#) [C45-3DC-72P](#) [C45-2DC-36](#) [C180-48P](#) [C45-4DC-24](#) [C45-2DC-24](#) [C45-3DC-24](#) [C45-6DC-24](#) [C45-3DC-24P](#) [C45-9DC-24](#) [C180T-60](#) [C45-3DC-144](#)