



LET	ECN	DESCRIPTION	DATE	INT
01		INITIAL RELEASE	04-08-12	Janves
02		ADDED CAVITY ID	05-22-12	JMM





SCALE 1/1

NOTES:


1. FOR LIST OF MATERIAL SEE:  
PL 115126-501, 115127-501
2. UNLESS OTHERWISE SPECIFIED:  
CORNERS SHOWN SHARP HAVE  
A RADIUS OF .01.
3. NO KNOCKOUTS, GATES OR FLASH  
ON THE EXTERIOR SURFACES.
4. FLASH PERMISSIBLE WITHIN .005 INCH.
5. KNOCKOUTS FLUSH TO .005 BELOW SURFACE.
6. TEXTURE: EDM #33
7. INTERIOR FINISH: SPI C3 OR BETTER
8. FOR ALL OTHER DIMENSIONS,  
SEE DRAWING: 115119-01



SECTION A-A



CAVITY ID:  
COPY 1.25 TALL  
RAISED 0.05 TO 0.1



SECTION B-B

**PACNTEC**  
Subsidiary of LaFrance Corp.

One LaFrance way, Concordville, Pa. 19332-5002 U.S.A.

NAME	DATE	CN-R SERIES
Janves	04-08-12	END CAP, USB-B
CHECK: Ted	04-08-12	
APPROVE: JMM	04-23-12	
MATERIAL:	PROCESS: INJ MOLDED	SCALE: 2:1
MOLD TOLERANCE: PRODUCT WILL BE PRODUCED PER SPI-SPE INSTITUTE PRODUCT STANDARDS AND TOLERANCES		
MACHINED: ANGLES: DECIMALS: XX ± .02 XXX ± .010		
COLOR: SEE PARTS LIST		
CLASS:		
PART #	DRAWING NUMBER	REV
115121-01	115121-01	02
SHEET 1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PacTec:

[69942-510-039 K-CM6-X450-BONE Kit](#)