


New  
**BK80AAAB**  
AAA size(HR11/45)

Old  
(HHR80AAAB)

Button top type

**B** type

**■ Dimensions (with tube)**




**■ Specifications**



Diameter		10.5 +0 / -0.7 mm	
Height		44.5 +0 / -1.0 mm	
Approximate Weight		13 g	
Nominal Voltage		1.2 V	
Discharge Capacity	Average <sup>*1</sup>	780 mAh	
	Rated (min.)	750 mAh	
Approx. Internal impedance at 1000Hz at charged state.		30 mΩ	
Charge	Standard	75 mA X 16 hrs.	
	Rapid <sup>*3</sup>	750 mA X 1.2 hrs.	
Ambient Temperature	Charge	Standard	0 °C to 45 °C
		Rapid	0 °C to 40 °C
	Discharge		-10 °C to 65 °C
	Storage	<1 year	-20 °C to 35 °C
<6 months		-20 °C to 45 °C	
<1 month		-20 °C to 55 °C	
<1 week		-20 °C to 65 °C	

\*1 After charging at 0.1 It for 16 hours, discharging at 0.2 It.  
 \*2 For reference only.  
 \*3 Need specially designed control system. Please contact Panasonic for details.

**■ Typical charge characteristics**



**■ Typical discharge characteristics**



Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge/discharge specs, warning label contents and unit design.

\*The data in this document are for descriptive purposes only and are not intended to make or imply any guarantee or warranty.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[HHR-70AAB27](#) [BK-80AAAB9B](#)