

LT4H-W Digital Timer (DIN□48)

Related Information

- General terms and conditions F-3 ■ Selection guide P.1383~
 ■ Options P.1423~



8-pin type



11-pin type



Screw terminal type

panasonic.net/id/pidsx/global

Features

- **Wide time range**
Operation time range: 0.01 sec. to 9999 hours.
- **Bright and easy-to-read display**
Bright 2-color back light LCD display.
- **Simple operation**
Seesaw buttons make operating.
- **Short body**
70.1 mm **2.760 in** (Pin type)
64.5 mm **2.539 in** (Screw terminal type)
- **IP66 compliant for resistance against negative environmental influences (only when panel surface uses rubber gasket)**
- **Screw terminal (M3.5) and pin types are both standard options**
- **Replaceable panel cover**
Panel design can be changed from standard (ash gray) to black (sold separately).

Time selectable

Mode selectable

DIN□48

IP66

Easy-to-read, user-friendly twin timers with a short body

PRODUCT TYPES

Product name	Time range	Operation mode	Output	Operating voltage	Power down insurance	Terminal type	Model No.
LT4H-W digital timer	99.99 s (0.01 s~) 999.9 s (0.1 s~) 9999 s (1 s~) 99 min59 s (1 s~) 999.9 min (0.1 min~) 99 h59 min (1 min~) 999.9 h (0.1 h~) 9999 h (1 h~)	Pulse input: • Delayed one shot • OFF-start flicker • ON-start flicker Integrating input: • Delayed one shot • OFF-start flicker • ON-start flicker	Relay (1c)	100 to 240 V AC	Available	8 pins	LT4HW8-AC240V
						11 pins	LT4HW-AC240V
				24 V AC		Screw terminal	LT4HW-AC240VS
						8 pins	LT4HW8-AC24V
				11 pins		LT4HW-AC24V	
				Screw terminal		LT4HW-AC24VS	
			Transistor (1a)	12 to 24 V DC		8 pins	LT4HW8-DC24V
						11 pins	LT4HW-DC24V
						Screw terminal	LT4HW-DC24VS
				100 to 240 V AC		8 pins	LT4HWT8-AC240V
						11 pins	LT4HWT-AC240V
						Screw terminal	LT4HWT-AC240VS
				24 V AC		8 pins	LT4HWT8-AC24V
						11 pins	LT4HWT-AC24V
						Screw terminal	LT4HWT-AC24VS
				12 to 24 V DC		8 pins	LT4HWT8-DC24V
						11 pins	LT4HWT-DC24V
						Screw terminal	LT4HWT-DC24VS

* A rubber gasket (ATC18002) and a mounting frame (AT8-DA4) are included.

FIBER SENSORS

LASER SENSORS

PHOTOELECTRIC SENSORS

MICRO PHOTOELECTRIC SENSORS

AREA SENSORS

SAFETY LIGHT CURTAINS / SAFETY COMPONENTS

PRESSURE / FLOW SENSORS

INDUCTIVE PROXIMITY SENSORS

PARTICULAR USE SENSORS

SENSOR OPTIONS

SIMPLE WIRE-SAVING UNITS

WIRE-SAVING SYSTEMS

MEASUREMENT SENSORS

STATIC CONTROL DEVICES

LASER MARKERS

PLC

HUMAN MACHINE INTERFACES

ENERGY MANAGEMENT SOLUTIONS

FA COMPONENTS

MACHINE VISION SYSTEMS

UV CURING SYSTEMS

Timers

Time Switches

Counters

Hour Meters

Options

Limit Switches

Temperature Controllers

Solenoids

Fan Motors

Selection Guide

LT4H series

QM4H

PM4S

PM4H series

S1DXM-A/M

S1DX

PMH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[LT4HW-DC24V](#) [LT4HW-AC240VS](#) [LT4HW-AC240V](#)