

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIE

NOTES:

- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. TERMINATED WITH (8 POSITION) MODULAR PLUGS AT BOTH ENDS PER T568B.
4. CONSTRUCTED WITH STRANDED CAT6 UTP 24AWG CM PATCH CABLE
5. MATERIALS:
PLUG: POLYCARBONATE
BOOT: CLEAR PVC
6. NOMINAL CABLE JACKET DIAMETER IS 0.235 IN (5.97MM)

STRAIN RELIEF BOOT

T568B WIRING SCHEME

PLUG POSITION:

1
2
3
4
5
6
7
8

CABLE WIRE:
WHITE/ORANGE
ORANGE
WHITE/GREEN
BLUE
WHITE/BLUE
GREEN
WHITE/BROWN
BROWN

IDENTIFICATION LABEL

TANGLE-FREE LATCH

MODULAR PLUG

PLUG POSITION 1

CABLE COLORS	** = COLOR
OFF WHITE	--
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
ORANGE	OR
VIOLET	VL

SEE SHEET 2 FOR
PATCH CORD LENGTHS
AND PART NUMBERS

PART NUMBER		UTPSPXX**Y	
TITLE			
TX6 PLUS UTP PATCH CORDS (CM)			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479NV/00	
DATASET FILE NAME		M02479NV_DC360/00E	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ± .03 [.8]		.XXX ± .010 [.3]	
ANGLES ±		THIRD ANGLE PROJECTION	
DRAWN BY		DATE	
NER		3-28-06	
CHK		WJC	
SCALE		NONE	
DRAWING NUMBER:		02479-360	
REV		DATE	
BY		CHK	
APR		DESCRIPTION	
ECN		SHT 1 OF 2	
SIZE		A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[UTPSP12BUY](#) [UTPSP40RDY](#) [UTPSP80RDY](#) [UTPSP140RDY](#) [UTPSP120RDY](#) [UTPSP100RDY](#) [UTPSP80BUY](#)
[UTPSP80GY](#) [UTPSP30Y](#) [UTPSP7ORY](#) [UTPSP25BLY](#) [UTPSP6BLY](#) [UTPSP3BLY](#) [UTPSP15Y](#) [UTPSP6ORY](#)
[UTPSP2GRY](#) [UTPSP15YLY](#) [UTPSP5ORY](#) [UTPSP1YLY](#) [UTPSP10BLY](#) [UTPSP2YLY](#) [UTPSP15ORY](#) [UTPSP7BLY](#)
[UTPSP8RDY](#) [UTPSP20GRY](#) [UTPSP3ORY](#) [UTPSP6VLY](#) [UTPSP25RDY](#) [UTPSP1ORY](#) [UTPSP15BLY](#)
[UTPSP7VLY](#) [UTPSP20YLY](#) [UTPSP4GRY](#) [UTPSP6GRY](#) [UTPSP4Y](#) [UTPSP1RDY](#) [UTPSP25GRY](#) [UTPSP15RDY](#)
[UTPSP5VLY](#) [UTPSP1BLY](#) [UTPSP6BUY](#) [UTPSP10ORY](#) [UTPSP30BUY](#) [UTPSP1GRY](#) [UTPSP4BUY](#) [UTPSP25YLY](#)
[UTPSP10YLY](#) [UTPSP6Y](#) [UTPSP20BUY](#) [UTPSP4ORY](#) [UTPSP14BLY](#) [UTPSP40BUY](#) [UTPSP15VLY](#) [UTPSP5BLY](#)
[UTPSP6YLY](#) [UTPSP8YLY](#) [UTPSP8BUY](#) [UTPSP20BLY](#) [UTPSP3VLY](#) [UTPSP4YLY](#) [UTPSP2Y](#) [UTPSP6RDY](#)
[UTPSP17BUY](#) [UTPSP35GRY](#) [UTPSP18BUY](#) [UTPSP20ORY](#) [UTPSP20VLY](#) [UTPSP2BLY](#) [UTPSP4GY](#)
[UTPSP17BLY](#) [UTPSP11VLY](#) [UTPSP40VLY](#) [UTPSP19BLY](#) [UTPSP16YLY](#) [UTPSP35VLY](#) [UTPSP40GY](#)
[UTPSP13Y](#) [UTPSP8Y](#) [UTPSP4RDY](#) [UTPSP16GRY](#) [UTPSP11Y](#) [UTPSP9VLY](#) [UTPSP4VLY](#) [UTPSP19VLY](#)
[UTPSP35ORY](#) [UTPSP30VLY](#) [UTPSP2RDY](#) [UTPSP8BLY](#) [UTPSP11YLY](#) [UTPSP19BUY](#) [UTPSP17YLY](#)
[UTPSP25VLY](#) [UTPSP16VLY](#) [UTPSP8GRY](#) [UTPSP9RDY](#) [UTPSP11BLY](#) [UTPSP11GRY](#) [UTPSP35Y](#)
[UTPSP25GY](#) [UTPSP13YLY](#)