


2

1



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT P/N	WEIGHT
CPPA48FM6VNSBL	14.0 LB/10 PCS (6353.9 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE FLUSH MOUNT PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:  
(1) - 48 PORT STAMPING  
(4) - 12 POSITION FACEPLATE (ASSEMBLED TO PANEL)  
(1) - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)  
(1) - SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.



PART NUMBER		PRODUCT SPEC/PKG SPEC	
CPPA48FM6VNSBL		N/A	
I.I. NUMBER		WORK INSTRUCTION	
N/A		N/A	
TITLE			
MINI-COM ANGLED 48 PORT FLUSH MOUNT MODULAR 6-PACK PATCH PANEL WITH VERTICAL NUMBERING SEQUENCE			
CUSTOMER DRAWING			
ITEM REVISION NAME			
M01667AG/00			
DATASET FILE NAME			
M01667AG_DC17/00B			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.x ± .1 [ 2.54 ] .xxx ± .005 [ .127 ] .xx ± .01 [ .25 ] ANGLES ± 5 °		PANEL: 18 GAGE GALVANNEALED- BLACK PAINT WITH WHITE LETTERING	
		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		01667-17	
DRAWN BY	DATE	CHK	SCALE
BJN	5-3-12	JAV	N/A
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	1-9-14	BJN	JAV	MMR	P/N WAS NON-STANDARD BEFORE; MAKING NEW STANDARD P/N	01667-17
R	5-3-12	BJN	JAV	JAV	RELEASED TO PRODUCTION	01667-17

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CPPA48FM6VNSBL](#)