



NOTES, UNLESS OTHERWISE SPECIFIED:

Panduit Tool Number CT-1104 is used to install single and dual wire Panduit insulated and non-insulated loose piece ferrules.

Crimps the following types:

- FTD type: 2 x 10 [6.0mm²] AWG insulated ferrules
- FSD and FSF type: #8 [10.0mm²] – #6 [16.0mm²] AWG insulated ferrules
- F type: #8 [10.0mm²] – #6 [16.0mm²] AWG non-insulated ferrules

TOOL FEATURES INCLUDE:

1. Self-adjusting crimp die for Insulated and non-insulated ferrules. Ferrule size dependent on wire gage. Refer to ferrule packaging for proper ferrule and wire combinations.
2. Controlled cycle mechanism prevents tool from opening before crimp cycle is complete.
3. Manual release lever, push forward in the event that controlled cycle mechanism must be released.
4. Resilient grips to prevent operator fatigue.
NOTE: The grips are NOT intended to insulate against electrical shock.

TOOL WEIGHT: 10.6 oz. (300 gr.)

DIMENSIONS SHOWN IN PARENTHESES ARE MILLIMETERS.

F:\wrkgpr\rvusers\ENGR DOCS\CUSTOMER DRAWINGS\TP25122B01_02 CT-1104 CD.doc

							CT-1104						
							CUSTOMER DRAWING						
							ITEM REVISION NAME:		TP25122B01_02		PANDUIT		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL:		SEE NOTES		
							(.x) ± — (.xxx) ± — (.xx) ± — ANGLES ± —		DRAWING NUMBER:				
							THIRD ANGLE PROJECTION		TP25122B01				
02	6-26-14	BLR	DP	DP	UPD TOOL HEAD GRAPHIC	4754	DRAWN BY: BLR		DATE: 3-29-06	CHK SRRE	SCALE NONE	SHT 1 OF 1	SIZE B
01	4-02-13	BLR	BJPU	ABJ	UPD TEMPLATE, BRANDING	4609							
00	3-29-06	BLR	SRRE	RFL	RELEASED	4195							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

CT-1104