



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	MAX. BUNDLE DIA [mm]	LENGTH ±.1 [2]
MS4W63T15-L4	304	4" [102]	18.0" [457]
MS4W63T15-L6	316		
MS6W63T15-L4	304	6" [152]	24.4" [620]
MS6W63T15-L6	316		
MS8W63T15-L4	304	8" [203]	30.7" [780]
MS8W63T15-L6	316		
MS10W63T15-L4	304	10" [254]	37.0" [940]
MS10W63T15-L6	316		



- NOTES: 1. APPLICATION TOOLS: BT2MS75, BT2HT
2. ALL DIMENSIONS IN [] ARE mm.
3. FOR MATERIAL SEE TABLE.
4. TOLERANCES (UNLESS OTHERWISE SPECIFIED):
.X ± .03 [.8]
.XX ± .02 [.5]
.XXX ± .010 [.25]

							TITLE					
							METAL STRAPPING .625 [15.88] WIDE					
							CUSTOMER DRAWING					
							ITEM REVISION NAME			PANDUIT		
							N41152BS/03					
							DATASET FILE NAME					
							N41152BS/03					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.127] .XX ± .01 [.25] ANGLES ± 5 °			MATERIAL: SEE NOTES		
3	02.24.15	BDK	SKB	RGR0	UPDATED TITLE BLOCK AND BORDER	N41152BS_DC	THIRD ANGLE PROJECTION			DRAWING NUMBER: N41152BS_DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							BRH	9/03	EJD	FULL		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[MS10W63T15-L4](#) [MS6W63T15-L4](#) [MS4W63T15-L4](#) [MS8W63T15-L4](#) [MS8W63T15-L6](#)