



2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT CONTROL.



PANDUIT PART NUMBER	WEIGHT	VOLUME CU. IN./CC
JB1-A	0.17 LB [75.9 G]	22.9 [376]

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. ADHESIVE PRESSURE SENSITIVE FOAM .040 (1.0) THICK WITH PROTECTIVE LINER IS PROVIDED FOR EASE OF MOUNTING.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.
4. BREAKOUTS ARE PROVIDED FOR LDS, LD & LDPH RACEWAYS.
5. BEAKOUTS TO ACCOMODATE CONDUIT SIZES OF 1/2" 3/4" & 1" DIAMETERS.



<div>3</div> <div>02-21-13</div> <div>JBN</div> <div>RTFI</div> <div>RTFI</div> <div>G. UPDATED DRAWING BORDER & TITLE BLOCK</div> <div>35541-53</div>						TITLE		ONE PIECE JUNCTION BOX JB1-A	
						CUSTOMER DRAWING			
						ITEM REVISION NAME		D35541DQ/00	
						DATASET FILE NAME		D35541DQ_DC_JB1/00C	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		<div>PANDUIT</div> <div>MATERIAL:</div> <div>POLYSTYRENE</div>	
						<div>.X ±</div> <div>.XX ± .03 [.8]</div> <div>.XXX ±</div> <div>ANGLES ±</div>		<div>DRAWING NUMBER:</div> <div>35541-53</div>	
						<div>THIRD ANGLE PROJECTION</div>			
						<div>DRAWN BY</div> <div>PM</div>		<div>DATE</div> <div>10-15-96</div>	
						<div>CHK</div> <div>CEF</div>		<div>SCALE</div> <div>NONE</div>	
								<div>SHT 1 OF 1</div>	
								<div>SIZE</div> <div>A</div>	

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[JB1IG-A](#)