


4

PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEETS PER PKG.	STANDARD PKG. QTY.
C061X030FJJ	GMP05	0.61 [15.49] X 0.30 [7.62]	325	16	5000

1. MILLIMETERS ARE IN [].



							TITLE C061X030FJJ LASER/INKJET LABELS CUSTOMER DRAWING					
							ITEM REVISION NAME I00673CH/01			PANDUIT MATERIAL: SEE TABLE DRAWING NUMBER: C10172		
							DATASET FILE NAME I00673CH_DC_C10172/01B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .12 [3.05] .xxx ± .025 [.635] .xx ± .062 [1.57] ANGLES ± THIRD ANGLE PROJECTION					
1	9/23/15	RVU	SEWH	JHAC	UPDATE ON PANDUIT LOGO. REMOVE NOTE 1. ADD .875. UPDATE TOLERANCES, TABLE AND TITLE. 2 PLCS.	GAECN03061						
0	4/14/03	RVU	DWY		DRAWING RELEASE.	3237						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY RVU	DATE 4/14/03	CHK JHAC	SCALE NTS	SHT 1 OF 1	SIZE A

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

C061X030FJJ