

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
FRSHC4**2 (SEE NOTE 1)	78.74 IN $\pm$ .18 IN (2000.0mm $\pm$ 4.6mm)	2.43 LB (1102g)	0.37 LB/FT (5.4g/cm)
FRSHC4**6 (SEE NOTE 1)	72.00 IN $\pm$ .18 IN (1828.8mm $\pm$ 4.6mm)	2.22 LB (1007g)	0.37 LB/FT (5.4g/cm)

# NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- THE FIBERRUNNER 4x4 SPLIT HINGED COVER REQUIRES NO TOOLS FOR INSTALLATION. THE SPLIT HINGED COVER CREATES A 3/4" (19.1) RADIUS OPENING TO ALLOW FOR NEW CABLES TO BE ADDED WITHOUT THE NEED FOR REMOVING THE COVERS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



							TITLE					
							FIBERRUNNER 4X4 SPLIT HINGED COVER					
							FRSHC4**2, FRSHC4**6					
							CUSTOMER DRAWING					
							ITEM REVISION NAME		<div>PANDUIT</div>			
							D37847CD/01					
							DATASET FILE NAME					
							D37847CD_DC_FRSHC4/01B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:			
							.X ± .XX ± .03 [ .8 ]		PVC			
							.XXX ± ANGLES ±		DRAWING NUMBER:			
							<div>THIRD ANGLE PROJECTION</div>		37847 - 48			
3	05-15-13	JBN	RTFI	RN	H. UPDATED DRAWING BORDER & TITLE BLOCK	37847-48						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							JHNU	07-13-01	DJWA	NONE		A

2

1

B

A

A

A

D10100DA/15

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FRSHC4BL6](#)