


**Notes:**

1. 600V max voltage rating
2. 257°F (125°C) max temperature rating of insulation material .
3. Stranded copper wire only
4. Material:
 - A. Stamping - brass, tin plated
 - B. Sleeve - copper or brass, tin plated.
 - C. Housing - Nylon type 6/6. Colors are translucent.
5. SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
6. Dimensions in bracket are in mm Or mm²


CERTIFIED
 LR31212


LISTED
 20H3
 E78522

Base part number	Wire range AWG (mm ²)	Tab size	Housing color	A ± .03 (.8)	W ± .02 (.5)	Max. Insul.	F ± .02 (.5)	Wire Strip length +1/32, -0 (+0.8, -0)	Crimp tools
DNF18-250FI	22-18 (0.5-1.0)	.250X.032 (6.3X.8)	Red	.94 (23.9)	.36 (9.1)	.14 (3.6)	.21 (5.3)	9/32 (7.1)	CT-100A CT-600-A CT-1550 CT-1551
DNF14-250FI	16-14 (1.5-2.5)	.250X.032 (6.3X.8)	Blue	.94 (23.9)	.36 (9.1)	.16 (4.1)	.24 (6.1)		CT-2400 W/CT-2455 CRIMP HEAD CT-2500
DNF10-250FI	12-10 (4.0-6.0)	.250X.032 (6.3X.8)	Yellow	.95 (24.1)	.36 (9.1)	.22 (5.6)	.27 (6.9)		CT-100, CT-100A, CT-460, CT-550 CT-600-A, CT-1551, CT-2500

						PANDUIT CORP. TINLEY PARK, ILLINOIS			
06	8/11	SHOR	MODIFIED NOTE #5, ADDED INSTALLATION TOOLS			FULLY INSULATED (STD NYLON) FEMALE DISCONNECTS SLEEVED BARREL (LOOSE PIECE)			
04	1/10	LM	Removed hidden lines for clarity						
REV	DATE	BY	DESCRIPTION	PM	CUST	DRAWN BY	CHK'D	SCALE	DRAWING NO.
						ES		NONE	A41672

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DNF18-250FI-M](#) [DNF18-250FI-L](#) [DNF14-250FI-L](#)